



A HIGHLY INNOVATIVE,
THUMB-ACTIVATED SEAR RELEASE.

THE VERSA FEATURES HARDENED 440C STAINLESS INTERNALS, WITH SIMPLE-TO-ADJUST TENSION AND TRAVEL SCREWS. THE HANDLE IS A FULLY RADIUSED TWO-PIECE SYSTEM AND ALLOWS YOU TO ROTATE THE FINGER ATTACHMENT TO ONE OF FIVE LOCATIONS.

THE THUMB BARS, PEGS AND TRIGGER OPTIONS CAN BE CUSTOMIZED TO FIT ANY ARCHER. THE VERSA'S EXCLUSIVE DESIGN INCLUDES A BASE SYSTEM THAT HOLDS SEARS IN PLACE — PRODUCING THE BEST PERFORMING RELEASE AVAILABLE TODAY.

COMPLETE INSTRUCTIONS INCLUDED INSIDE PAGKAGE.

101 TUG BRANCH ROAD CLAY CITY, KY / 40312

**B3ARCHERY.COM 606.612.5215** 





- RED.
- BLUE
- BRASS



440C STAINLESS INTERNALS

MULTIPLE THUMB
ADJUSTMENTS



## **Adjustment Instructions**

## **Travel Adjustment**

- 1. THE CAP SCREW LOCATED IN THE TRIGGER AT THE BASE OF THE HANDLE IS YOUR TRAVEL ADJUSTMENT SCREW.
- 2. TO INCREASE TRAVEL, ROTATE THE CAP SCREW COUNTER-CLOCKWISE. TO DECREASE TRAVEL, ROTATE THE SCREW CLOCKWISE.

## **Tension Adjustment**

- 1. LOCATE THE SET SCREW ON THE SIDE OF YOUR RELEASE HANDLE. TURN THIS SET SCREW CLOCKWISE TO INCREASE TENSION AND COUNTER-CLOCKWISE TO DECREASE TENSION.
- 2. NEVER TURN MORE THAN 2 FULL TURNS (IN EITHER DIRECTION) FROM THE FACTORY SETTING.
- \*\*\*ALL ADJUSTMENTS SHOULD BE MADE IN 1/16TH TURN INCREMENTS.
- \*\*\*ALWAYS TEST YOUR RELEASE AFTER ANY ADJUSTMENTS ARE MADE.

## Finger Adjustment

- 1. LOOSEN THE 6-32 X 3/8 SCREW.
- 2. MOVE FINGER PIECE TO DESIRED LOCATION AND RE-TIGHTEN THE 6-32 x 3/8 SCREW.

DO NOT OVERTIGHTEN.

PLEASE TEST AFTER ANY ADJUSTMENT.



101 TUG BRANCH ROAD / CLAY CITY, KY / 40312 B3ARCHERY.COM / 606.612.5215

